

Specifications

Model name	bizhub 362 / bizhub 282
Type	Desktop/Console
Copy resolution	600x600dpi
Gradation	256
Memory capacity (Std/Max)	192MB standard (32MB used for file memory)
Hard disk	40GB (Optional)
Original type	Sheet, Book, 3-D objects
Max. original size	A3 (297 x 420mm) or 11"x17"
Output size	A3-A6 or 11"x17" - 5 1/2" x 8 1/2"
Image loss	Top & bottom edges: 4mm Right & left edges: 4mm
Warm-up time	14sec. or less (aux. power); 24sec. or less (main power) with std. config.
First copy time	bizhub 362: 4.8sec. or less, bizhub 282: 5.3sec. or less
Copy speed	bizhub 362: 36cpm (A4), 20cpm (A3); bizhub 282: 28cpm (A4), 17cpm (A3)
Magnification	Fixed ratio
	Enlargement 1:1.154/1.414/2.000
	Reduction 1:0.930/0.816/0.707/0.500
Zoom	25%-400% (in 0.1% increments)
Paper capacity	Std. 1,150, Max. 3,650 sheets
Paper weights	Top Tray, Middle Tray, Bottom Tray: 56-90g/m ²
	Multi Bypass: 91-210g/m ² (Thick paper and OHP sheets)
Multiple copy	1-999 sheets, Countdown, Interrupting capability
Duplex	Stackless ADU (standard)
Power requirements	AC220-240V 6.3A + up to 10% (50/60Hz)
Power consumption	1.3-1.47kW + up to 10%
Dimensions (W x D x H)	677mm x 710mm x 718mm
Weight	Approx. 74kg

Scanning Function Specifications

Size of originals	Max. A3
Scan resolution	200x100dpi, 200x200dpi, 400x400dpi, 600x600dpi
Speed (A4 crosswise)	41opm (600dpi), 70opm(200dpi) with RADF
Main functions	Scan to E-Mail, Scan to HDD (Box), Scan to FTP, Scan to PC (SMB), Scan to Internet Fax
Interface	Ethernet 10BASE-T / 100BASE-TX
Network protocol	SMTP, FTP, SMB
Operating systems	Windows NT4.0 SP6/2000, SP3/XP/XP64bit/Server2003/Server2003 64bit/Vista/Server2008 MacOS 9.2 or later/X 10.2.3,4/10.4 Intel or later
Data format	TIFF/PDF
Scanner driver	Network TWAIN Driver (HDD TWAIN) WSD (Win98SE/Me/NT4.0SP6/2000/XP/Server2003/Vista/Server2008)

Printer Specifications


Type	Embedded
Print system	Laser exposure
CPU	RM5231 (300MHz)
Memory	192MB RAM standard
Speed	bizhub 362: 36ppm (A4); bizhub 282: 28ppm (A4)
Hard disk	40GB (Optional)
Print resolution	600x600dpi
PDL	PCL6, PostScript [®] 3 Emulation
Network protocol	TCP/IP, IPX/SPX, SMB, LPD, IPP 1.1, SNMP, SMTP/POP3, HTTP, FTP and others
Operating systems	Windows NT4.0 SP6/2000, SP3/XP/XP64bit/Server2003/Server2003 64bit/Vista/Server2008 MacOS 9.2 or later/X 10.2.3,4/10.4 Intel or later
Fonts	PCL: 80 fonts, PS: 136 fonts
Interface	Ethernet 10BASE-T / 100BASE-TX, USB1.1 / 2.0 (full speed), Parallel Interface(Optional)

Fax Function Specifications (Optional FK-503 required)

Send size	Max. A3
Record size	Max. A3
Transmission standard	Super G3
Line density	8x3.851, 8x7.7, 8x15.4, 16x15.4 line/mm, 200x100dpi, 200x200dpi, 400x400dpi, 600x600dpi
Transmission speed	Less than 3 sec. (V.34, JBIG, A4 original)
Modem speed	2.4kbps-33.6kbps
Data compression method	MH/MR/MMR/JBIG
Communication line	Public Phone Line, Fax Communication Line
Scanning speed	Less than 3 sec.
Speed dial	540 numbers
Program dial	30 numbers (included in speed dial total)
Consecutive transmissions	300 locations

Converting paper weight Multiply g/m² weight x 0.636 x 0.939 (1kg = Approx. 1.66g/m²)

System Options



Product appearance, configuration and / or specifications are subject to change without notice.

- bizhub and PageScope are registered trademarks of KONICA MINOLTA BUSINESS TECHNOLOGIES, INC.
- Windows is a registered trademark of Microsoft Corporation.
- Adobe and PostScript are registered trademarks of Adobe Systems, Inc.
- All other brand and product names are registered trademarks or trademarks of their respective companies.
- As an ENERGY STAR Partner, KONICA MINOLTA BUSINESS TECHNOLOGIES, INC. has determined that this product meets the ENERGY STAR guidelines for energy efficiency.
- ENERGY STAR is a registered trademark in the U.S.

Ecology & Environment



KONICA MINOLTA copiers and multi-functional products are designed with the environment in mind.

- Energy Star
- RoHS Compliance
- WEEE Compliance
- Energy Conservation
- Emission reduction
- Use Recycled Materials
- Toner Recycle Mechanism
- Production at ISO Certified Factories

Requirements for safe use.

- Please read and follow the instruction manual to ensure safe operation.
- Only operate using appropriate power supply and voltage.
- Connecting the earth wire to an inappropriate place may cause explosion or electric shock. Please connect accordingly (Taiwan and the Philippines only).



KONICA MINOLTA

bizhub 362/282

Innovation Through
Communication
for a New Style of Business



KONICA MINOLTA
BUSINESS TECHNOLOGIES, INC.

1-6-1 Marunouchi Chiyoda-ku, Tokyo, Japan
<http://www.biz.konicaminolta.com>



This catalogue was printed using soy ink.

9251-3179-01 Printed in Japan

The essentials of imaging

